



Sensors > Piezo Film Sensors > PIEZO FILM LAB PRE-AMPLIFIER



Piezo Film Sensor Type: **Electronic Interface Product**

All PIEZO FILM LAB PRE-AMPLIFIER (3)

Features

Product Type Features

Piezo Film Sensor Type	Electronic Interface Product
------------------------	------------------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (18% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous



materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 1007214-1

AMPLIFIER&EU POWER SUPPLY PLUG

Customers Also Bought



TE Part #816961-SF

RT8522-6-10M0



TE Part #11029785-00

LAB AMPLIFIER W/O POWER CORD



TE Part #2-1437667-8

4DB-P108-05=4DB ASSEMBLY



TE Part #1622825-1

RL73K 2A R10 5% 5K RL




TE Part #1879208-3

CPF 0402 12R 0.1% 25PPM 1K RL



TE Part #6-1879377-6

CRGH0805 5% 470R 0.33W




TE Part #1-2176379-2

RQ 0805 140R 0.1% 10PPM 5K RL



TE Part #3-2176397-9

3502 39R 1%



TE Part #7-2176421-9

TLRP 2512 2.0W R012 1% 75PPM 4K RL



TE Part #6609104-9

PE0S0SS30=C1134

Documents

Datasheets & Catalog Pages

Piezo_Film_Lab_Amplifier



English